

M A X I C O M F O R T TM S E R I E S



Day Dreamer
PR-630
shown in Coffee Bean



Hazelnut

Calypso

Shiraz

Coffee Bean*
* upcharge applies



The DayDreamer with the exclusive PowerPillow™ provides the ultimate in position control. Recline back and adjust your head and neck using the exclusive powered head pillow. MaxiComfort combined with the PowerPillow offers maximum comfort options.

L

INDEPENDENCE
IN MOTION™
A DIVISION OF RESTORATIVE INNOVATIONS, INC.



610-630-8400



Day Dreamer



Power Articulation Head Forward



Power Articulation Head



Power Articulation Head Back

Model Number	PR-630
Size	Medium
Weight Capacity	375 Lb.
Recline Positions	MaxiComfort
Standard Fabrics	TBD
Fabric Options	None
Chaise Seat	YES
Coil Springs	NO
Back Type	Seam
Head Rest Cover	NO
Arm Covers	NO
Battery Back Up	YES
Overall Width	38"
Overall Height	44"
Width Between Arms	21"
Floor to Top of Seat	20"
Seat Depth	19.5"
Seat to Top of Back	28.5"
Seat to Top of Arm	5.5"
Seat Angle Raised	16°
Floor to Top of Foot Rest Reclined	23"
Floor to Top of Back Reclined	23.5"
Back Angle Closed	105°
Back Angle Reclined	175°
Foot Rest Angle Closed	90°
Foot Rest Angle Opened	180°
Distance Required from Wall Reclined	25.5
Extension reclined from Back of Seat to end of Foot Rest	42"
Life Time Warranty, Chair Frame, Lift Frame, Recline Mechanism	YES
Warranty on Electrical Parts	3 Yrs.
Pro Rated Years 4 Thru 7	YES
Warranty on Mechanical Labor	3 Yrs.
Warranty on Electrical Labor	1 Yr.
Removable Back Option Available	NO
Smart Tek System Standard	YES
Customizable	NO
Left Hand Control Option Available	NO
Extra Pocket Option Available	NO
Heat & Massage Option Available	NO
Foot Rest Extension Option Available	NO
Straight Lift Option Available	NO
User Height (suggested)	5'4" - 5'10"

Sizes may vary depending on fabric, filling material, upholstery and carpet thickness. All measurements taken on concrete floor using levels and metal rulers.



Battery Backup System

Batteries not included. Battery Backup System is designed to bring the chair from the reclined to the seated position in the event of a power outage.



Smart Tek

In the event of a malfunction, our patented SmartTek™ diagnostic system enables you to get your lift chair up and running quickly.

Literature is current at time of printing. Golden Technologies reserves the right to make changes to the product or literature at any time.



Complies with UL 73 and CSA C22.2 No. 68
Listing # E112417
FNAE 80-214A

